

## **CLB 2.65 60A**

- Used to sense the current load of a medical insulated power supply system, which is monitored by the insulation monitoring device from HAKEL.
- Available in the range of primary current 25 A to 100 A, secondary current 5 A.
- Construction is pluggable, is supplied in two dimensional versions, depending on the primary current.
- Designed for installation in an IPS panel, they can be mounted to the distribution board using reduction brackets (included), or using a DIN rail bracket (must be purchased separately).
- Alternatively, the transformer can be mounted directly on the copper profile, up to a maximum size of 20 x 10 mm.
- Work reliably with HAKEL HIG95-DELTA and HIG95+ insulation monitoring devices.

Туре		CLB 2.65 60A
Primary current		60 A
Secondary side current		5 A
Power	Р	2.5 W
Accuracy class		1
Overcurrent number (FS)		5
Transformer construction		Pluggable (without interrupting the primary conductor)
Frequency	f	50 ÷ 60 Hz
Housing material		Self-extinguishing
Recommended cross-section of connected conductors	S	$1.5 \div 2.5 \text{ mm}^2$
Operating position		Any
Operating temperature	Э	-25 ÷ 40 °C
Article number of DIN rail bracket		71 541
Designed according to standards		
Instrument transformers – General requirements		IEC 61869-1:2007
Instrument transformers - Additional requirements for current transformers		IEC 61869-2:2012
Application standards		
Low-voltage electrical installations – Medical locations		HD 60364-7-710:2012
Insulation monitoring devices for medical locations (MED-IMD)		IEC 61557-8:2014 annex A
Ordering, packaging and additional data		
Mass	m	660 g
Mass (including the packaging)	m	688 g
Packaging dimensions (H x W x D)		74 x 112 x 73 mm
Packaging value	V	0.61 dm <sup>3</sup>
Customs tariff no.		85043129
EAN code		8590681270929
Art. number		71 534






**The link in the QR code** leads to the online presentation of the **CLB 2.65 60A**. There, in addition to the always up-to-date data sheet, you will also find all diagrams and drawings, declarations of conformity, or 2D or 3D models and other necessary materials. For more information, visit **www.hakel.com** 



## Application wiring diagram (installation)



## Internal diagram

